



Model MSR Mechanical Setting Tools are used to mechanically set MMR Sleeve-Valve Cement Retainers. This tool incorporates both a stinger seal and mechanical setting function. In addition, it has a built-in snap-latch, allowing the tool to be latched into the cement retainer with set-down weight and released with either upstrain or right-hand rotation. The sleeve-valve on the cement retainer is in the open position while being run in the well. When the setting procedure is completed, the sleeve-valve may be closed by picking up two inches at the tools or opened by slacking off two inches. The snap-latch feature allows the sleeve-valve to be shifted open or closed while the tubing is still anchored to the retainer. Another feature of the tool provides for running the sleeve-valve either open or closed. Normally the valve is run open so the tubing may fill. However, for pressure testing the tubing, while running, the valve can be run closed. Cement Retainers can be set and pressure tested in a single trip.

- Special designed Bow Spring provide positive control and allows one size Mechanical Setting Tools to cover a large range of casing weight
- The Upper slips are held in a safe retracted position while running
- Allows users to set, pressure test tubing, and squeeze in a single trip
- Can quickly be configured to set MMR Cement Retainers or MMB Bridge Plugs
- These tools can be used to run a number of Competitive brand Baker style cement retainers
- These tools can run any standard Baker style plug or retainer

Part Number	Casing OD	Casing Wt. (T&C)	Tool OD
CPS0359005	4 ½ - 5	9.5-16.6 - 11.5-20.8	3.59
CPS0431005	5 1/2	13-23	4.31
CPS0470005	5 3/4	14-26	4.70
CPS0537005	6 5/8	17-32	5.37
CPS0568005	7	17-35	5.68
CPS0631005	7 5/8	20-39	6.31
CPS0712005	8 5/8	24-49	7.12
CPS0812005	9 5/8	29.3-58.4	8.12
CPS0943005	10 3/4	32.75-60.7	9.43
CPS0994005	11 3/4	60-83	9.94
CPS1043005	11 3/4	38-60	10.43
CPS1188005	13 3/8	48-80.7	11.88
CPS1412005	16	65-118	14.12

**Suite 245, 6025 - 12th Street S.E., Calgary, Alberta, Canada T2H 2K1**

**Tel. # (403)-543-0350, Fax. # (403)-543-0351**

<mailto:canam@canamservices.com>

[www.canamservices.com](http://www.canamservices.com)